

ÖLFLEX® CONTROL TM CY

ÖLFLEX® Control Cable PVC Screened 0.6/1kV UL TC-ER WTTC AWM600V OIL RES CSA AWM


ÖLFLEX® CONTROL TM CY: UL MTW TC-ER WTTC AWM 600V OIL RES II WET CSA AWM I/II A/B FT4, Screened PVC Power Control Cable 0.6/1 kV, Tray Exposed Run, Wind Turbine

Info

Torsion resistant for drip loops

Wide application range (NFPA 70/NEC)/ compliance with NFPA 79 for industrial machinery

EMC/Screened



Flame-retardant



Cold-resistant



Mechanical resistance



Oil-resistant



Interference signals



Torsion-resistant



UV-resistant

Benefits

Many certifications/ use types

Cost-saving, fast installation omitting protection systems

Last Update (14.04.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® CONTROL TM CY

Electromagnetic field screening
75 °C WET Rating + Sunlight Resistant Rating: Outdoor use in the USA

Application range

Industrial machinery, plant engineering in the USA
Unprotected 600V operation on cable tray in the USA, incl. 6 ft. Exposed Run laying sections for version with at least 3 conductors
Compliant with Tool machines: (UL) MTW
USA Wind Turbine Tray Cable (WTTC) for Wind Turbine Generators
Outdoor use and Direct Burial in the USA, per UL 1277

Product features

Flame-retardant according to CSA FT4
UL Vertical-Tray Flame Test
Oil-resistant according to UL OIL RES I & II
Technically resistant to sunlight and ozone
High degree of screening
low transfer impedance
(max. 250 Ω/km at 30 MHz)
Suitable for torsional applications which are typical for the loop in wind turbine generators (WTG)

Norm references / Approvals

USA: (UL) TC [E171371], -ER > 2 conductors, (UL) MTW [E155920], (UL) WTTC [E323700], (UL) THHN/THWN (> 1.5 mm²/16 AWG) [E172162], UL AWM Style 20886 [E100338]
Sunlight Resistant (Sun. Res.), Direct Burial (Dir. Bur.), Submersible Pump Cable (> 1.5 mm²/16 AWG, and < 8 conductors), (UL) PLTC (< 6 mm²/10 AWG) [E216027], (UL) ITC (< 6 mm²/10 AWG) [E196134], (UL) DP-1 [E233406]
UL OIL RES I/II, 75°C WET, 90°C DRY, NEC/NFPA 70, NFPA 79
CAN: c(UL) CIC/ TC 600V FT4 [E171371], CSA AWM I/II A/B FT1

Product Make-up

Fine-wire strand made of bare copper wires
Insulation: PVC with nylon sheath (PA skin)
Aluminum-coated foil
Tinned-copper braiding
Outer jacket: Specially formulated thermoplastic polymer
Color of the outer jacket: Gray

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0 Class-Description: Control cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class-Description: Control cable
Core identification code:	Black with white numbers
Conductor stranding:	Fine-wire, bare copper strand
Torsion movement in WTG:	TW-0 & TW-2, refer to Appendix T0
Minimum bending radius:	Static/Occ. moved: 5/20 x OD*
Nominal voltage:	UL/CSA: 600 V (TC, MTW, CIC), WTTC 1000 V UL AWM: 600 V CSA AWM: 1000 V IEC: U ₀ /U = 600/1000 V

Last Update (14.04.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® CONTROL TM CY

Test voltage:	2000 V
Protective conductor:	G = with GN-YE protective conductor X = without protective conductor
Temperature range:	-40°C (static)/ -25°C (occ. moved) to +90°C (AWM: +105°C)

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil \leq 30 kg or \leq 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 610 m drum or 8 x 76 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

*OD = Outer diameter

ÖLFLEX® CONTROL TM CY

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
ÖLFLEX® CONTROL TM CY				
281803CY	3 G 1.0	8.1	49.5	119
281804CY	4 G 1.0	8.6	60.2	137
281805CY	5 G 1.0	9.3	81.4	149
281807CY	7 G 1.0	10	101.1	193
281812CY	12 G 1.0	12.8	161.4	281
281818CY	18 G 1.0	15.5	228.2	438
281825CY	25 G 1.0	17.5	326.4	574
281603CY	3 G 1.5	8.8	65	144
281604CY	4 G 1.5	9.4	81.9	173
281605CY	5 G 1.5	10.2	99.1	189
281607CY	7 G 1.5	11.1	140.4	246
281612CY	12 G 1.5	15	225.2	426
281618CY	18 G 1.5	17.2	321.7	552
281403CY	3 G 2.5	9.7	105.7	180
281404CY	4 G 2.5	10.4	135.6	223
281405CY	5 G 2.5	11.5	160.3	268
281407CY	7 G 2.5	12.4	213	327
281204CY	4 G 4.0	12.3	198.5	315
281205CY	5 G 4.0	14.2	242.7	388
281004CY	4 G 6.0	15.3	284.236	552
280804CY	4 G 10.0	18.5	458.4	857

Last Update (14.04.2020)

©2020 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

 You can find the current technical data in the corresponding data sheet:
 PN 0456 / 02_03_16