

FIPLOCK® ONE 90° M

Conduit fitting system for highest requirements, suitable for FIPLOCK® PA6 / PA12

FIPLOCK® ONE 90° M

Info

New conduit fitting system with innovative locking system



Rail



Good chemical resistance



Flame-retardant



Halogen-free



Cold-resistant



Maximum vibration protection



Mechanical resistance



Assembly time



Low weight

Last Update (02.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FIPLOCK® ONE 90° M



Optimum strain relief



Robust



Reliability



UV-resistant



Waterproof



Benefits

Very high tensile strength due to all around tooth system
 Ensures mounting safety due to integrated coding system
 Excellent IP rating
 Cost-saving due to quick and easy installation

Application range

Suitable for FIPLOCK® PA6 / PA12
 Demand of increased liquid tightness
 For indoor and outdoor use

Product features

All around locking mechanism due to 360° tooth system
 Locking mechanism with integrated coding system
 Extended sealing range across multiple corrugated conduit waves

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Certifications:	IEC EN 61386-23 EN 45545-2 HL3
Colour delivered:	Grey (RAL 7005) Black (RAL 9005), UV-resistant
Material:	PA 6 Halogen-free Fire behaviour according to UL 94V-0
Protection rating:	IP66/IP67/IP68/IP69
Temperature range:	-45°C to +120°C

Last Update (02.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FIPLOCK® ONE 90° M

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

FIPOLOCK® ONE 90° M

Article number	Metric size	Thread length mm	Clear opening (mm)	Design	Suitable for FIPOLOCK® PA6 / PA12	Colour	Pieces / PU
FIPOLOCK® ONE 90° M - black							
61804458	12 x 1.5	11	7	90° corner angle	7	black	10
61804459	12 x 1.5	11	7	90° corner angle	10	black	10
61804461	16 x 1.5	11	10	90° corner angle	10	black	10
61804463	16 x 1.5	11	10	90° corner angle	12	black	10
61804462	20 x 1.5	11	12	90° corner angle	10	black	10
61804464	20 x 1.5	11	12	90° corner angle	12	black	10
61804465	20 x 1.5	11	10.2	90° elbow angle	17	black	10
61804466	25 x 1.5	12	14.8	90° elbow angle	17	black	10
61804467	25 x 1.5	12	15.9	90° elbow angle	23	black	6
61804468	32 x 1.5	15	22.8	90° elbow angle	23	black	6
61804469	32 x 1.5	15	22.8	90° elbow angle	29	black	6
61804471	40 x 1.5	19	28.5	90° elbow angle	29	black	6
61804472	40 x 1.5	19	30.2	90° elbow angle	36	black	4
61804473	50 x 1.5	19	36.1	90° elbow angle	36	black	4
61804474	50 x 1.5	19	38.9	90° elbow angle	48	black	4
61804475	63 x 1.5	19	47.9	90° elbow angle	48	black	4
FIPOLOCK® ONE 90° M - grey							
61804476	12 x 1.5	11	7	90° corner angle	7	grey	10
61804477	12 x 1.5	11	7	90° corner angle	10	grey	10
61804478	16 x 1.5	11	10	90° corner angle	10	grey	10
61804481	16 x 1.5	11	10	90° corner angle	12	grey	10
61804479	20 x 1.5	11	12	90° corner angle	10	grey	10
61804482	20 x 1.5	11	12	90° corner angle	12	grey	10
61804483	20 x 1.5	11	10.2	90° elbow angle	17	grey	10
61804484	25 x 1.5	12	14.8	90° elbow angle	17	grey	10
61804485	25 x 1.5	12	15.9	90° elbow angle	23	grey	6
61804486	32 x 1.5	15	22.8	90° elbow angle	23	grey	6
61804487	32 x 1.5	15	22.8	90° elbow angle	29	grey	6
61804488	40 x 1.5	19	28.5	90° elbow angle	29	grey	6
61804489	40 x 1.5	19	30.2	90° elbow angle	36	grey	4
61804491	50 x 1.5	19	36.1	90° elbow angle	36	grey	4
61804492	50 x 1.5	19	38.9	90° elbow angle	48	grey	4
61804493	63 x 1.5	19	47.9	90° elbow angle	48	grey	4

Last Update (02.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16