

## SILVYN® LTP

SILVYN® LTP - black conduit with thick PVC jacket



Good chemical resistance



Mechanical resistance



Oil-resistant



Robust



UV-resistant



Waterproof

### Benefits

Protects against liquids

High-tensile

Robust

High crush-resistance

Largely resistant to oil and acids, UV-resistant

### Application range

Mechanical engineering

Outdoors

Transformer construction

Railway applications

Paper industry

Last Update (15.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SILVYN® LTP

### Product Make-up

Spirally-wound heavy metal protective conduit with roughened profile  
Plastic outer sheath

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001179 ETIM 5.0 Class-Description: Protective metallic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001179 ETIM 6.0 Class-Description: Protective metallic hose
Certifications:	IEC EN 61386-23
Colour delivered:	Black (RAL 9005), UV-resistant
Material:	Steel, galvanised PVC sheath
Temperature range:	-20°C to +105°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.



SILVYN® LTP

Article number	Nominal size	ID x OD mm	Bending radius (mm)	PU ring (m)
SILVYN® LTP				
61805400	10 - 1/4"	7.0 x 11.8	35	50
61805410	12 - 5/16"	10.0 x 14.2	40	50
61805420	16 - 3/8"	12.6 x 17.8	45	50
61805430	20 - 1/2"	16.0 x 21.1	65	50
61805440	25 - 3/4"	21.0 x 26.4	100	25
61805450	32 - 1"	26.5 x 33.1	135	25
61805460	40 - 1 1/4"	35.4 x 41.8	175	10
61805470	50 - 1 1/2"	40.4 x 47.9	230	10
61805480	63 - 2"	51.6 x 59.7	280	10

Last Update (15.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16