

FIPLOCK® ONE CLICK-M

Conduit fitting system for highest requirements, suitable for FIPLOCK® PA6 / PA12

FIPLOCK® ONE CLICK-M

Info

New conduit fitting system with innovative locking system
Integrated SKINTOP® cable strain relief



Rail



Good chemical resistance



Flame-retardant



Halogen-free



Cold-resistant



Maximum vibration protection



Mechanical resistance



Assembly time



Low weight

Last Update (02.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FIPLOCK® ONE CLICK-M



Optimum strain relief



Robust



Reliability



UV-resistant



Waterproof



Benefits

Very high tensile strength due to all around tooth system
 Ensures mounting safety due to integrated coding system
 Excellent IP rating
 Cost-saving due to quick and easy installation

Application range

Suitable for FIPLOCK® PA6 / PA12
 Demand of increased liquid tightness
 For indoor and outdoor use

Product features

All around locking mechanism due to 360° tooth system
 Locking mechanism with integrated coding system
 Extended sealing range across multiple corrugated conduit waves
 Cable strain relief

Technical Data

| | |
|------------------------|---------------------------------------------------------------------------------------------------------|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose |
| Certifications: | IEC EN 61386-23 EN 45545-2 HL3 |
| Colour delivered: | Grey (RAL 7005) Black (RAL 9005), UV-resistant |
| Material: | PA 6 Halogen-free Fire behaviour according to UL 94V-0 |
| Protection rating: | IP66/IP67/IP68/IP69 |
| Temperature range: | -45°C to +120°C |

Last Update (02.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FIPLOCK® ONE CLICK-M

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

FIPLOCK® ONE CLICK-M

| Article number | Metric size | Clamping range in mm | SW 1/2 mm | Thread length mm | Wall thickness, S (mm) | Suitable for FIPLOCK® PA6 / PA12 | Colour | Pieces / PU |
|-----------------------------------|-------------|----------------------|-------------|------------------|------------------------|----------------------------------|--------|-------------|
| FIPLOCK® ONE CLICK-M black | | | | | | | | |
| 61804874 | M 16 | 5.0 - 9.0 | 22.0 / 20.0 | 8 | 1.0 - 4.0 | 10 | black | 10 |
| 61804875 | M 16 | 5.0 - 9.0 | 22.0 / 22.0 | 8 | 1.0 - 4.0 | 12 | black | 10 |
| 61804876 | M 20 | 7.0 - 13.0 | 27.0 / 22.0 | 8 | 1.0 - 4.0 | 12 | black | 10 |
| 61804877 | M 20 | 7.0 - 13.0 | 27.0 / 27.0 | 8 | 1.0 - 4.0 | 17 | black | 10 |
| 61804878 | M 25 | 9.0 - 17.0 | 32.0 / 27.0 | 8 | 1.0 - 4.0 | 17 | black | 10 |
| 61804879 | M 25 | 9.0 - 17.0 | 32.0 / 36.0 | 8 | 1.0 - 4.0 | 23 | black | 6 |
| 61804880 | M 32 | 11.0 - 20.0 | 40.0 / 36.0 | 8 | 1.0 - 4.0 | 23 | black | 6 |
| 61804881 | M 32 | 11.0 - 20.0 | 40.0 / 41.0 | 8 | 1.0 - 4.0 | 29 | black | 6 |
| FIPLOCK® ONE CLICK-M grey | | | | | | | | |
| 61804882 | M 16 | 5.0 - 9.0 | 22.0 / 20.0 | 8 | 1.0 - 4.0 | 10 | grey | 10 |
| 61804883 | M 16 | 5.0 - 9.0 | 22.0 / 22.0 | 8 | 1.0 - 4.0 | 12 | grey | 10 |
| 61804884 | M 20 | 7.0 - 13.0 | 27.0 / 22.0 | 8 | 1.0 - 4.0 | 12 | grey | 10 |
| 61804885 | M 20 | 7.0 - 13.0 | 27.0 / 27.0 | 8 | 1.0 - 4.0 | 17 | grey | 10 |
| 61804886 | M 25 | 9.0 - 17.0 | 32.0 / 27.0 | 8 | 1.0 - 4.0 | 17 | grey | 10 |
| 61804887 | M 25 | 9.0 - 17.0 | 32.0 / 36.0 | 8 | 1.0 - 4.0 | 23 | grey | 6 |
| 61804888 | M 32 | 11.0 - 20.0 | 40.0 / 36.0 | 8 | 1.0 - 4.0 | 23 | grey | 6 |
| 61804889 | M 32 | 11.0 - 20.0 | 40.0 / 41.0 | 8 | 1.0 - 4.0 | 29 | grey | 6 |

Last Update (02.05.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16