

## FIPLOCK® ONE Coupler

Conduit fitting system for highest requirements, suitable for FIPLOCK® PA6 / PA12

FIPLOCK® ONE Coupler

### Info

New conduit fitting system with innovative locking system



Rail



Good chemical resistance



Flame-retardant



Halogen-free



Cold-resistant



Maximum vibration protection



Mechanical resistance



Assembly time



Low weight

Last Update (22.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## FIPLOCK® ONE Coupler



Optimum strain relief



Robust



Reliability



UV-resistant



Waterproof



### Benefits

Very high tensile strength due to all around tooth system  
Ensures mounting safety due to integrated coding system  
Excellent IP rating  
Cost-saving due to quick and easy installation

### Application range

Suitable for FIPLOCK® PA6 / PA12  
Demand of increased liquid tightness  
For indoor and outdoor use

### Product features

All around locking mechanism due to 360° tooth system  
Locking mechanism with integrated coding system  
Extended sealing range across multiple corrugated conduit waves

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose

Certifications:

IEC EN 61386-23

EN 45545-2 HL3

Colour delivered:

Grey (RAL 7005)

Black (RAL 9005), UV-resistant

Material:

PA 6

Halogen-free

Fire behaviour according to UL 94V-0

Protection rating:

IP66/IP67/IP68/IP69

Temperature range:

-45°C to +120°C

Last Update (22.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## FIPLOCK® ONE Coupler

**Note**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**FIPLOCK® ONE Coupler**

| Article number       | Nominal size | Suitable for FIPLOCK® PA6 / PA12 | Colour | Pieces / PU |
|----------------------|--------------|----------------------------------|--------|-------------|
| FIPLOCK® ONE-C black |              |                                  |        |             |
| 61805027             | 12           | 12                               | black  | 10          |
| 61805028             | 17           | 17                               | black  | 10          |
| 61805029             | 23           | 23                               | black  | 6           |
| 61805030             | 29           | 29                               | black  | 6           |
| 61805031             | 36           | 36                               | black  | 4           |
| 61805032             | 48           | 48                               | black  | 4           |
| FIPLOCK® ONE-C grey  |              |                                  |        |             |
| 61805033             | 12           | 12                               | grey   | 10          |
| 61805034             | 17           | 17                               | grey   | 10          |
| 61805035             | 23           | 23                               | grey   | 6           |
| 61805036             | 29           | 29                               | grey   | 6           |
| 61805037             | 36           | 36                               | grey   | 4           |
| 61805038             | 48           | 48                               | grey   | 4           |

Last Update (22.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## FIPLOCK® ONE Coupler

