

## SILVYN® MSK-M ATEX BRUSH

SILVYN® MSK-M ATEX BRUSH - nickel-plated brass conduit fitting for ATEX environment, integrated cable strain relief

### Info

IECEx approval worldwide

Optimum 360° screen contact



Wide clamping range



Mechanical resistance



Assembly time



Optimum strain relief



Robust



Reliability



Integrated SKINTOP<sup>®</sup> cable gland



Interference signals

### Benefits

Easy installation

Faster, easier screen contact

Optimum cable and conduit strain relief

Last Update (12.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SILVYN® MSK-M ATEX BRUSH

Maximum cable sealing  
Wide clamping range

### Application range

Devices, machines and apparatus of enhanced safety protection type "e", dust ignition proof "t"  
Chemical and petrochemical industry  
Plant engineering  
Used in areas where cables and wires need additional mechanical protection

### Product features

Combination of SILVYN® and SKINTOP®

### Product Make-up

SILVYN® conduit connection via inner sleeve and cap nut  
Metric connection thread acc. to DIN EN 60423

### Note

To be used in Ex environment only in combination with metal conduits without a plastic jacket

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001180 ETIM 5.0 Class-Description: Screw connection for protective metallic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001180 ETIM 6.0 Class-Description: Screw connection for protective metallic hose
Certifications:	CE 0637 Ex II 2G Ex eb IIC Ex II 1D Ex ta IIIC IECEX IBE 13.0033X
Material:	Basis type: Body: nickel-plated brass Conduit connector seal: CR/NBR Tube seal: TPE EMC brush: brass
Tests:	DIN EN 60079-0 DIN EN 60079-7 DIN EN 60079-31
Protection rating:	Cable: IP 68 Conduit: IP 40 with SILVYN® AS, EDU-AS, EMC AS-CU
Temperature range:	-30 °C to +90 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SILVYN® MSK-M ATEX BRUSH**

Article number	Metric size	Clamping range in mm	Clear opening (mm)	Suitable for conduit Ø (mm)	Pieces / PU
SILVYN® MSK-M ATEX BRUSH for SILVYN® AS					
55506042	25 x 1.5	9.0 - 17.0	14.5	21	10
55506043	32 x 1.5	11.0 - 21.0	19.5	27	1
55506044	40 x 1.5	19.0 - 28.0	26.5	36	1
55506045	50 x 1.5	27.0 - 35.0	36	45	1
55506030	63 x 1.5	34.0 - 45.0	45.5	56	1
SILVYN® MSK-M ATEX BRUSH for SILVYN® EDU-AS / EMC AS-CU					
55506031	25 x 1.5	9.0 - 17.0	14.5	21	10
55506032	32 x 1.5	11.0 - 21.0	19.5	27	1
55506033	40 x 1.5	19.0 - 28.0	26.5	36	1
55506034	50 x 1.5	27.0 - 35.0	36	45	1
55506035	63 x 1.5	34.0 - 45.0	45.5	56	1

Last Update (12.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03\_16