

SILVYN® MSK-U-M

Universal metric threaded coupler with integrated cable strain relief, for use with conduit fittings

SILVYN® MSK-U-M - nickel-plated brass conduit coupler, with integrated cable strain relief

Info

Integrated SKINTOP® cable strain relief



Wide clamping range



Maximum vibration protection



Mechanical resistance



Optimum strain relief



Robust



Reliability



Integrated SKINTOP® cable gland

Benefits

Optimum cable and conduit strain relief

Maximum cable sealing

Fast and easy assembly

Wide clamping range

Anti-turn protection

Last Update (05.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® MSK-U-M

Application range

In combination with metric threaded conduit fittings

Used in areas where cables and wires need to be provided with strain relief and additional sealing

Product features

Combination of SILVYN® and SKINTOP®

Note

For suitable accessories, refer to SKINTOP® metric accessories

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001180 ETIM 5.0 Class-Description: Screw connection for protective metallic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001180 ETIM 6.0 Class-Description: Screw connection for protective metallic hose
Material:	Body: nickel-plated brass Insert: Polyamide Sealing ring: CR/NBR O-ring: NBR
Protection rating:	Cable: IP 68 Conduit: depending on the used conduit system
Temperature range:	Fixed: -40°C up to +100°C Dynamic: -25°C up to + 100°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® MSK-U-M

Article number	Metric size	Clamping range in mm	Suitable gland size	Pieces / PU
55506129	12 x 1.5	3.5 - 7.0	M 12 x 1,5	5
55506130	16 x 1.5	4.5 - 10.0	M 16 x 1,5	5
55506131	20 x 1.5	7.0 - 13.0	M 20 x 1,5	5
55506132	25 x 1.5	9.0 - 17.0	M 25 x 1,5	5
55506133	32 x 1.5	11.0 - 21.0	M 32 x 1,5	5

Last Update (05.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16