

SILVYN® EC

SILVYN® EC - end cap for parallel corrugated conduits



Wide clamping range



Low weight



Reliability



Temperature-resistant



UV-resistant

Benefits

Cable damage can be prevented
Additional sealing
Easy to assemble

Application range

In combination with protective conduit:
SILVYN® FPAS
Intersection or end sleeve

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000519

ETIM 5.0 Class-Description: Terminal sleeve for protective hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000519

ETIM 6.0 Class-Description: Terminal sleeve for protective hose

On request:

SILVYN® REC for FPAS67

Colour delivered:

Black (RAL 9005), UV-resistant

Material:

NEC: PA66

REC: TPE

Temperature range:

NEC: -50 °C to +135 °C

Last Update (29.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® EC

REC: -50°C to +120°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® EC

Article number	Nominal size	Clamping range in mm	Clear opening (mm)	Suitable for SILVYN® FPAS	Pieces / PU
SILVYN® NEC					
55507097	16	-	10.5	16	10
55507098	21	-	15	21	10
55507099	28	-	20	28	10
55507100	34	-	25.5	34	10
55507101	42	-	32	42	10
55507102	54	-	43.5	54	10
SILVYN® REC					
55507040	10	3 - 7	-	10	10
55507041	13	3 - 7	-	13	10
55507042	16	3 - 11	-	16	10
55507043	21	3 - 15	-	21	10
55507044	28	3 - 21	-	28	10
55507045	34	3 - 25	-	34	10
55507046	42	5 - 34	-	42	10
55507047	54	5 - 46	-	54	10

Last Update (29.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

SILVYN® EC

