

SILVYN® FPAC

SILVYN® FPAC - polyamide conduit coupler



Halogen-free



Maximum vibration protection



Mechanical resistance



Assembly time



Optimum strain relief



Space requirement



Temperature-resistant

Benefits

Fast assembly
High tensile strength
Optional extension of parallel corrugated conduits

Application range

In combination with protective conduit:
SILVYN® FPAS
Conduit coupler for extension

Product features

Last Update (18.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® FPAC

Removeable with a screwdriver

Note

UV-resistant and weather-resistant

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001172 ETIM 5.0 Class-Description: Coupler for corrugated plastic hoses
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001172 ETIM 6.0 Class-Description: Coupler for corrugated plastic hoses
Certifications:	IEC EN 61386-23
On request:	IP68 / IP69 version
Colour delivered:	Grey (RAL 7031) Black (RAL 9005), UV-resistant
Material:	PA66 Halogen-free
Protection rating:	IP 66
Temperature range:	-50 °C to +135 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.



SILVYN® FPAC

Article number	Nominal size	Suitable for SILVYN® FPAS	Pieces / PU
SILVYN® FPAC black			
55507005	16	16	10
55507006	20	20	10
55507015	21	21	10
55507016	25	25	10
55507025	28	28	10
55507035	34	34	10
55507036	42	42	2
55507037	54	54	2
SILVYN® FPAC grey			
55507000	16	16	10
55507001	20	20	10
55507010	21	21	10
55507011	25	25	10
55507020	28	28	10
55507030	34	34	10
55507031	42	42	2
55507032	54	54	2

Last Update (18.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16