SILVYN® HIPROSILTAPE

SILVYN® HIPROSILTAPE - silicone tape for SILVYN® HIPROJACKET

Info
Outstanding protection for extreme impact of heat



Benefits
Heat-resistant
Flexible
The protection rating increases to IP67 if SILVYN® HIPROSILTAPE is also used
Temporarily reduces the temperature in the conduit by up to 30 %

Application range
Heavy industry, iron and steel works, foundries, glass and ceramic processing, chemical industries
Steel industry
Railway applications / vehicle construction
Mechanical engineering
Used in areas where cables and wires are exposed to extreme heat

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000128 ETIM 5.0 Class-Description: Adhesive tape
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000128 ETIM 6.0 Class-Description: Adhesive tape
Colour delivered:	Red
Material:	Silicone-rubber compound, self-vulcanising, halogen-free
Temperature range:	-55 °C to +260 °C permanent temp.

Note
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2024 Lapp Group - Technical changes reserved

SILVYN® HIPROSILTAPE

Article number	Nominal size	ID x OD mm	PU ring (m)
SILVYN® HIPROSILTAPE			
61713040	25	25.0 x 0.5	11

Last Update (22.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16