

SILVYN® HCC

SILVYN® HCC is a unique protection conduit with metric dimensions



Good chemical resistance



Halogen-free



Low weight



UV-resistant

Benefits

Dimensionally stable
Flexible
Lightweight
Crush-resistant

Application range

Mechanical engineering
Apparatus construction
Building Automation
Moving applications
Outdoors

Product features

Conduit with full metric design
Halogen and cadmium-free
Abrasion-resistant
High resistance to oil, petrol, acids and other chemicals

Product Make-up

Fine-profile corrugated polyamide 6 conduit

Note

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® HCC

UV-resistant and weather-resistant

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001175 ETIM 5.0 Class-Description: Corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001175 ETIM 6.0 Class-Description: Corrugated plastic hose
Colour delivered:	Black (RAL 9005), UV-resistant
Material:	PA6 Halogen-free
Temperature range:	-25°C to +100°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® HCC

Article number	Nominal size	ID x OD mm	Bending radius (mm)	Suitable for SILVYN® FPAG-M / FLEXILOK-M	Suitable for SILVYN® HG-M	PU ring (m)
SILVYN® HCC						
61793970	13	9.8 x 13.0	25	16 + 20	-	50
61793980	16	11.8 x 16.0	30	16 + 20	-	50
61793990	20	14.8 x 20.0	40	20	-	50
61794000	25	19.1 x 25.0	50	25	-	50
61794010	32	24.3 x 32	65	32	-	25
61794020	40	30.2 x 40	85	-	40	25
61794030	50	40.1 x 50	110	-	50	25
61794035	63	52.5 x 63	130	-	63	25

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16