

## SILVYN® CNP

SILVYN® CNP is a liquidtight conduit with a PVC inner conduit and nylon jacket, UL/CSA listed



Good chemical resistance



Mechanical resistance

### Benefits

Protection against mechanical stress  
Protects against liquids  
Bendable  
Highly oil and acid-resistant

### Application range

Mechanical engineering  
Robot-building  
Vending machine construction  
Exporters

### Product Make-up

PVC inner conduit  
Nylon braiding  
Plastic outer sheath

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001177

ETIM 5.0 Class-Description: Protective plastic hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001177

ETIM 6.0 Class-Description: Protective plastic hose

Certifications:

UL 1660

Colour delivered:

Orange

Last Update (09.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

**SILVYN® CNP**

Material:	PVC compound with nylon fabric
Protection rating:	IP 67
Temperature range:	-20°C to +60°C CSA: -18°C to +75°C Short-term: up to +80°C

**Note**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SILVYN® CNP**

Article number	Nominal size	ID x OD mm	Static/dynamic bending radius in mm	Suitable for SILVYN® CNP	PU ring (m)
SILVYN® CNP					
61712930	3/8"	12.6 x 19.4	70.0 / 100.0	1/2"	76
61722330	1/2"	16.1 x 23.4	90.0 / 125.0	1/2"	60
61722340	3/4"	21.0 x 29.5	115.0 / 160.0	3/4"	53
61712460	1"	26.5 x 36.3	170.0 / 200.0	1"	30
61712910	1 1/4"	31.5 x 46.0	200.0 / 240.0	1 1/4"	15
61722270	1 1/2"	40.4 x 52.4	230.0 / 290.0	1 1/2"	15
61722320	2"	52.4 x 66.6	260.0 / 350.0	2"	15

Last Update (09.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03.16