

SILVYN® SPLIT COV-M

SILVYN® SPLIT COV is a divisible conduit fitting for subsequent installation with the divisible conduit SILVYN® SPLIT



Halogen-free



Assembly time



Temperature-resistant



UV-resistant

Benefits

Fast and easy assembly
Subsequent mountable conduit insertion

Application range

In combination with protective conduit:
SILVYN® SPLIT
Mechanical engineering
Electrical industry
Used in areas where cables and wires need to be protected after assembly

Product features

divisible counter nut with metric thread

Note

UV-resistant and weather-resistant

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class-Description: Screw connection for corrugated

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® SPLIT COV-M

Colour delivered:	plastic hose Black (RAL 9005), UV-resistant
Material:	Halogen-free PA
Temperature range:	-40 °C to +120 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.



SILVYN® SPLIT COV-M

Article number	Metric size	Suitable for SILVYN® SPLIT	Pieces / PU
SILVYN® SPLIT COV-M (counter nut not included)			
61806680	16 x 1.5	10	100
61806681	20 x 1.5	14	100
61806682	25 x 1.5	20	50
61806683	32 x 1.5	23	50
61806684	40 x 1.5	37	25
61806685	50 x 1.5	45	25

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16