


FKK Flat cable wedge clamps

FKK 08 wedges for fastening flat cables up to 10 mm cable thickness

Info

Suitable mounting plates in the web catalog



Benefits

On the shaft side, the mounting plate can be screwed onto the wall or bolted or welded to the rail bracket
The mounting plate can be bolted or welded to the lift cage

Application range

Mounting flat control cables

Product Make-up

The small wedge-shaped cable clamp can hold up to 2 flat cables, the big one up to 3 flat cables

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002407

ETIM 5.0 Class-Description: Accessories for installation rail current/data cable

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002407

ETIM 6.0 Class-Description: Accessories for installation rail current/data cable

Info:

Clamping force (at overall cable thickness):

FKK 08: 2-10mm = 600-800N

FKK 07: 2-9mm / 16-17mm = 800N

Minimum insert depth for wedge:

FKK 08: 60% = 60mm

FKK 07: 60% = 90mm

Material:

Polyamide 6.6 - halogen-free

Temperature range:

Operating temperature: -20 °C to +50 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (02.01.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FKK Flat cable wedge clamps

Article number	Article designation	Number of cables	Max. total cable length (mm)	Weight (g)	Pieces / PU
52026051	FKK 08	1-2	50 x 10	103	1
52026050	FKK 07	1-3	90x17	349	1

Last Update (02.01.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FKK Flat cable wedge clamps

