


DIN-Coil conductor end sleeves

Insulated conductor end sleeves in strips/coils



Halogen-free

Application range

Insulated conductor end sleeves in strips, DIN 46228, Part 4

DIN strips, available in coils of up to 3000 items for working with automatic crimping machines

Included

Coil diameter: approx. 25 cm

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000005

ETIM 5.0 Class-Description: Cable end sleeve

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000005

ETIM 6.0 Class-Description: Cable end sleeve

Material:

Copper/PP

Surface: tin-plated

Temperature range:

Permanent load -5°C up to +105°C, temporary load +120°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

DIN-Coil conductor end sleeves

Article number	Article designation	For mm ²	Colour	l1 mm	l2 mm	d1 mm	d2 mm	R mm	Contents (unit)
61802052	DIN coil 0.5	0.5	white	14.5	8	1.1	2.6	3.5	3000 x 1
61802054	DIN coil 0.75	0.75	grey	14.5	8	1.3	2.8	3.6	3000 x 1
61802056	DIN coil 1.0	1	red	14.5	8	1.5	3	3.9	3000 x 1
61802058	DIN coil 1.5	1.5	black	14.5	8	1.8	3.4	4.2	2500 x 1
61802060	DIN coil 2.5	2.5	blue	14.5	8	2.3	4.2	5	1500 x 1

Last Update (14.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16