

## KEB 1025 crimping pliers

KEB 1025 ergonomic crimping pliers/tool for conductor end sleeves up to 25 mm<sup>2</sup>



### Benefits

Unique mechanism reduces the manual force from 450 N to 250 N  
Handles suit both large and small hands  
Locking function that is released only after completion of the pressing operation  
Tested for a minimum of 80,000 pressings

### Application range

Mini-force tools for pressing insulated and non-insulated conductor end sleeves from 10 - 25 mm<sup>2</sup>

### Product features

Emergency release, if the pressing operation needs to be interrupted

### Norm references / Approvals

Tested in accordance with DIN standard EN 60352-2

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000168

ETIM 5.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000168

ETIM 6.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection

Note:

Crimping profile: Particular developed form in the style of a W-crimp

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

## KEB 1025 crimping pliers

Article number	Article designation	For mm <sup>2</sup>	Crimping profile	Weight (kg)	Length (mm)	Pieces / PU
61791065	KEB 1025	10 - 25	trapezoid	0.5	220	1

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16