

PVX 1300 pressing pliers battery-operated

PVX 1300: Battery powered pressing pliers for cable lugs

Info

NEW: two-stage DUAL crimping technique (first hexagonal pressing, then additional mandrel pressing)



Benefits

- Pressure strength control using pressure monitoring
- Buzzing signal and flashing light if right pressure is not achieved
- Display with information on the tool and service interval
- Single-handed operation for easy handling
- Rapid feed for more efficient crimping

Application range

Battery powered crimp tool for crimping of CU terminals KRF/KRT 10-400 mm²
Same accessories as V1311-A pliers

Product features

- Crimps/charge: 60-120 depending on size and temperature
- Battery type: Makita 5 Ah
- Charging time: 40 min

Included

Supplied with robust plastic case, battery charger and instruction manual
Pressing dies and die holders need to be ordered separately

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000168

ETIM 5.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000168

ETIM 6.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection

Note:

Crimping profile: DUAL (hexagonal + mandrel) or hexagonal
Pressing force: 124 kN (13 t)

PVX 1300 pressing pliers battery-operated

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

PVX 1300 pressing pliers battery-operated

Article number	Article designation
61813872	Crimping tool PVX 1300

Last Update (07.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16