

SILVYN® MSK-M FPS-EDU

SILVYN® MSK-M FPS-EDU - nickel-plated brass conduit fitting with integrated cable strain relief

Info

Integrated SKINTOP® cable strain relief



Wide clamping range



Maximum vibration protection



Assembly time



Optimum strain relief



Robust



Integrated SKINTOP® cable gland

Benefits

Optimum cable and conduit strain relief
Maximum cable sealing
Fast and easy assembly
Wide clamping range
Anti-turn protection

Application range

In combination with protective conduit:
SILVYN® FPS-EDU
Plant engineering

Last Update (05.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® MSK-M FPS-EDU

Mechanical engineering

Used in areas where cables and wires need to be provided with strain relief and additional sealing

Product features

Combination of SILVYN® and SKINTOP®

Product Make-up

SILVYN® conduit connection via inner sleeve and cap nut

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001180 ETIM 5.0 Class-Description: Screw connection for protective metallic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001180 ETIM 6.0 Class-Description: Screw connection for protective metallic hose
Material:	Basis type: Body: nickel-plated brass Conduit connector seal: CR/NBR Tube seal: TPE
Protection rating:	Cable: IP 68 Conduit: IP 54 with SILVYN® FPS-EDU
Temperature range:	-30°C to +100°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® MSK-M FPS-EDU

Article number	Metric size	Clamping range in mm	Clear opening (mm)	Suitable for SILVYN® FPS-EDU	Pieces / PU
55506146	16 x 1.5	4.5 - 10.0	8.5	14	5
55506147	20 x 1.5	7.0 - 13.0	11	17	5
55506148	25 x 1.5	9.0 - 17.0	14.5	21	5
55506149	32 x 1.5	11.0 - 21.0	19.5	27	5
55506150	40 x 1.5	19.0 - 28.0	27.5	36	1
55506151	50 x 1.5	27.0 - 35.0	35.5	45	1
55506152	63 x 1.5	34.0 - 45.0	47	56	1

Last Update (05.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16