

## KNIPEX Alligator® Water pump plier

KNIPEX Insulated pliers for gripping and cutting work

### Info

Good access to the workpiece due to slim size



### Benefits

Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required

High ergonomics thanks to multi-component handles

Insulated handles allow working under voltage up to 1000V

### Application range

Insensitive to dirt due to robust construction, hence particularly suitable for outdoor work

### Product features

9-notch adjustment positioning

High wear resistance of the gripping surfaces

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000164

ETIM 5.0 Class-Description: Water pump plier

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000164

ETIM 6.0 Class-Description: Water pump pliers

Certifications:

Insulated according to IEC 60900, applicable up to 1000V AC / 1500V DC

VDE-tested

Material:

Chrome vanadium electric steel, forged, multi stage oil-hardened

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.



## KNIPEX Alligator® Water pump plier

Article number	Article designation	Clamping width mm	Jaw distance mm	Weight (kg)	Length (mm)
62120505	Water pump plier WPZI 25	50	46	0.374	250