

## SILVYN® SI

SILVYN® SI - grey soft PVC conduit



Low weight



Flame-retardant

### Benefits

Protection against dust  
 Protection against humidity  
 Low abrasion protection

### Application range

Easy cable protection  
 Additional insulation  
 Bundling and guiding of cables and wires

### Product features

Flexible  
 Soft

### Product Make-up

Soft-PVC conduit

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001177

ETIM 5.0 Class-Description: Protective plastic hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001177

ETIM 6.0 Class-Description: Protective plastic hose

Note:

Flame-retardant and self-extinguishing

Dielectric strength: 25 kV/mm

Last Update (05.07.2019)

©2019 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

**SILVYN® SI**

Colour delivered:	Tear-resistance: 23 N/mm <sup>2</sup>
Material:	Shore A hardness: 75 °C to 90 °C
Temperature range:	Silver grey (RAL 7001)
	Soft PVC
	-5 °C to +80 °C

**Note**

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

**SILVYN® SI**

Article number	ID x OD mm	Suitable for SILVYN® SSV-M/SSVZ-M	Suitable for SILVYN® SSV/SSVZ	Suitable for SILVYN® SCH	PU ring (m)
SILVYN® SI					
61713210	7.0 x 9.0	12/1 / -	-	10 - 16 S	50
61713240	9.0 x 12.0	12/2 / -	-	10 - 16 S	50
61713270	11.0 x 14.0	16/1 / -	-	10 - 16 S	50
61713300	13.0 x 16.0	16/2 / -	-	12 - 20 S	50
61713330	14.0 x 18.0	20/1	-	12 - 20 S	50
61713360	18.0 x 22.0	20/3	13,5/1	16 - 25 S	50
61713390	23.0 x 28.0	25	21	25 - 40 S	50
61713420	32.0 x 38.0	32 / 32/2	29/2	32 - 50 S	50

Last Update (05.07.2019)

©2019 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03\_16