



## SILVYN® SP-PU

SILVYN® SP-PU - black PUR conduit



SILVYN® SSV/SSV-M + SCH  
IP 54



SILVYN® SSVZ/SSVZ-M + SCH  
IP 54



SILVYN® USK/USK-M  
IP 54



SILVYN® SCH



Good chemical resistance



Mechanical resistance



UV-resistant



Waterproof

### Benefits

Protection against mechanical stress  
Abrasion protection  
Protection against chemicals  
UV-resistant and weather-resistant

### Application range

Cable protection  
Bundling and guiding of cables and wires  
Outdoors  
In harsh environment

### Product features

Tear-resistant  
Oil and petrol-resistant  
Halogen-free  
Resistant to microbes  
Dimensionally stable

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SILVYN® SP-PU

### Product Make-up

Hard PVC inner spiral  
Polyurethane outer sheath

### Technical Data

|                        |  |
|------------------------|--|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC001177<br>ETIM 5.0 Class-Description: Protective plastic hose |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC001177<br>ETIM 6.0 Class-Description: Protective plastic hose |
| Certifications:        | IEC EN 61386-23  |
| Colour delivered:      | Black (RAL 9005), UV-resistant   |
| Material:              | PUR with hard PVC spiral<br>Fire behaviour according to UL 94V-0                   |
| Temperature range:     | -20°C to +90°C   |

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SILVYN® SP-PU**

| Article number | ID x OD mm  | Bending radius (mm) | Suitable for SILVYN® SSV-M/SSVZ-M | Suitable for SILVYN® USK-M | Suitable for SILVYN® SSV/SSVZ | Suitable for SILVYN® USK | Suitable for SILVYN® SCH | PU ring (m) |
|----------------|-------------|---------------------|-----------------------------------|----------------------------|-------------------------------|--------------------------|--------------------------|-------------|
| SILVYN® SP-PU  |             |                     |                                   |                            |                               |                          |                          |             |
| 61793620       | 10.0 x 14.0 | 50                  | 16 x 1,5/1                        | 12 x 1,5                   | 9/1                           | 9                        | 10 - 16 S                | 25          |
| 61793630       | 12.0 x 16.0 | 60                  | 16 x 1,5/2                        | 16 x 1,5                   | 9/2                           | 11                       | 12 - 20 S                | 25          |
| 61793640       | 14.0 x 18.0 | 70                  | 20 x 1,5/1                        | -                          | 11/1                          | 13,5                     | 12 - 20 S                | 25          |
| 61793650       | 16.0 x 20.0 | 80                  | 20 x 1,5/2                        | 20 x 1,5                   | 11/2                          | 16                       | 16 - 25 S                | 25          |
| 61793660       | 22.0 x 27.0 | 110                 | 25 x 1,5                          | 25 x 1,5                   | -                             | 21                       | 20 - 32 S                | 25          |
| 61793670       | 30.0 x 36.0 | 150                 | 32 x 1,5                          | 32 x 1,5                   | 29/1                          | 29                       | 25 - 40 S                | 25          |
| 61793680       | 38.0 x 44.0 | 200                 | 40 x 1,5                          | 40 x 1,5                   | 36                            | 36                       | 32 - 50 S                | 25          |

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16