

## Insulating tube ISY

Insulating tube ISY made of PVC for bundling and insulating cables.



### Application range

Insulating tube  
For insulation of connections

### Product features

Smooth surface

### Norm references / Approvals

IEC 60684-3-100

### Note

Not suitable for shrinking

### Design

Colours: black RAL 9005, white similar to RAL 9003

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC002254 ETIM 5.0 Class-Description: Cable insulation hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC002254 ETIM 6.0 Class-Description: Cable insulation hose
Note:	Dielectric strength: 14 kV/mm
Info:	Without fabric
Colour delivered:	Black and white
Material:	Soft PVC
Temperature range:	-20 °C ... +85 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

**Insulating tube ISY**

Article number	Article designation	Colour	Internal Ø x wall thickness (mm)	Material	PU (m)
61793030	ISY 2	black	2 x 0.4	PVC	1000
61793040	ISY 3	black	3 x 0.4	PVC	750
61793050	ISY 4	black	4 x 0.5	PVC	500
61793060	ISY 5	black	5 x 0.6	PVC	500
61793070	ISY 6	black	6 x 0.6	PVC	400
61793080	ISY 7	black	7 x 0.7	PVC	500
61793090	ISY 8	black	8 x 0.7	PVC	500
61793100	ISY 9	black	9 x 0.7	PVC	400
61793110	ISY 10	black	10 x 0.7	PVC	300
61793116	ISY 10	white	10 x 0.7	PVC	300
61793119	ISY 16	black	16 x 1	PVC	150

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16