

SILVYN® CNP

SILVYN® CNP is a liquidtight conduit with a PVC inner conduit and nylon jacket, UL/CSA listed



Good chemical resistance



Mechanical resistance

Benefits

Protection against mechanical stress
Protects against liquids
Bendable
Highly oil and acid-resistant

Application range

Mechanical engineering
Robot-building
Vending machine construction
Exporters

Product Make-up

PVC inner conduit
Nylon braiding
Plastic outer sheath

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001177

ETIM 5.0 Class-Description: Protective plastic hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001177

ETIM 6.0 Class-Description: Protective plastic hose

Certifications:

UL 1660

Colour delivered:

Orange

Last Update (14.02.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® CNP

Material:	PVC compound with nylon fabric
Protection rating:	IP 67
Temperature range:	-20°C to +60°C CSA: -18°C to +75°C Short-term: up to +80°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.



SILVYN® CNP

Article number	Nominal size	ID x OD mm	Static/dynamic bending radius in mm	Suitable for SILVYN® CNP	PU ring (m)
61722320	2"	52.4 x 66.6	260.0 / 350.0	2"	15
SILVYN® CNP					
61712930	3/8"	12.6 x 19.4	70.0 / 100.0	1/2"	76
61722330	1/2"	16.1 x 23.4	90.0 / 125.0	1/2"	60
61722340	3/4"	21.0 x 29.5	115.0 / 160.0	3/4"	53
61712460	1"	26.5 x 36.3	170.0 / 200.0	1"	30
61712910	1 1/4"	31.5 x 46.0	200.0 / 240.0	1 1/4"	15
61722270	1 1/2"	40.4 x 52.4	230.0 / 290.0	1 1/2"	15

Last Update (14.02.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16