

Cable trolley system for C-rails stainless steel

Lapp Group offers a cable trolley system both for flat and round cables.

Info

Configuration tool on our homepage (Knowledge center-cable accessories)



Benefits

Gentle cable clamps prevent the cables from sharp bends
Dustproof ball bearing (wheels) guarantee smooth running in the rails

Application range

Crane and conveying machinery
For hoisting equipment and conveyor systems
Mechanical engineering
Washing plants
Not suitable for applications in explosive environments

Note

Round- and flat cables are not allowed to be combined side by side or below each other
Don't assemble more than three clamps for round cables below each other
Bending radius on the bracket corresponds to a fixed installation

Included

Delivery length of the C-profile 6 m

Product Make-up

The installation of a system depends on various criteria, e.g. maximum cable slack (cable weight) and working length.

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002935

ETIM 5.0 Class-Description: Accessories for cable carrying system

General:

Max. cable load: 20 kg

Material:

Metal parts: Acid proof steel SS 2343

Nuts and bolts: Acid proof steel A4

Clamps: Polyamide 6

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

Cable trolley system for C-rails stainless steel

Temperature range: -40 °C to +120 °C

Note

CIBES® is a registered trade mark of INOMEK AB

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Cable trolley system for C-rails stainless steel

Article number	Article designation	System	Max. flat cable dimensions mm	max. round cable diameter mm	Pieces / PU
Cable trolley flat cables					
62200453	Cable trolley flat C30 15x54 stainless	C30 stainless steel	15.0 x 54.0	-	1
62200462	Cable trolley flat C30 30x54 stainless	C30 stainless steel	30.0 x 54.0	-	1
62200630	Towing trolley flat C30 30x54 stainless	C30 stainless steel	30.0 x 54.0	-	1
62200640	End clamp flat C30 30x54 stainless	C30 stainless steel	30.0 x 54.0	-	1
Cable trolley round cable					
62200120	Cable trolley round C30 stainless	C30 stainless steel	-	-	1
62200680	Towing trolley round C30 stainless	C30 stainless steel	-	-	1
62200130	Clamp round 10-16mm stainless	C30 stainless steel	-	10.0 - 16.0	1
62200463	Clamp round 17-25mm stainless	C30 stainless steel	-	17.0 - 25.0	1
62200700	Clamp round 26-36mm stainless	C30 stainless steel	-	26.0 - 36.0	1
62200690	End clamp round stainless	C30 stainless steel	-	-	1
Fastening components					
62200454	C Profile rail 6m C30 stainless	C30 stainless steel	-	-	1
62200600	Track coupler C30 stainless	C30 stainless steel	-	-	1
62200610	Support brackets flex. C30 stainless	C30 stainless steel	-	-	1
62200487	Support brackets wall C30 stainless	C30 stainless steel	-	-	1
62200620	End stop C30 stainless	C30 stainless steel	-	-	1
62200660	Support arm 800mm C30 stainless	C30 stainless steel	-	-	1
62200650	Towing arm 400mm stainless	C30 stainless steel	-	-	1
62200670	Girder clips stainless	C30 stainless steel	-	-	1