

## PEW 8.185 crimping pliers

PEW 8.185 Crimping tool/pliers for pressing insulated conductor end sleeves with a square crimping, made in Germany, quick and reliable



### Benefits

- Ergonomic handles and very low hand force required
- Uniform feed on the crimp die guarantees exact crimping profiles
- DIN compliant crimping quality due to integral lock (self-releasing mechanism)
- Automatic self-adjustment to requested wire size

### Application range

For pressing insulated and non-insulated conductor end sleeves  
Could be used up to a sleeve length of 20 mm (for sleeves longer than 12 mm at least 2 crimps are necessary)

### Product features

Made of chromium-plated tool steel

### Note

End sleeves up to 12 mm only needs to be pressed once, longer end sleeves (up to a 20 mm lengths) needs to be pressed at least twice

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000168

ETIM 5.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000168

ETIM 6.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.



## PEW 8.185 crimping pliers

Article number	Article designation	For mm <sup>2</sup>	Crimping profile	Weight (kg)	Length (mm)	Pieces / PU
61813736	PEW 8.185	0.08 - 16	square	0.38	180	1

Last Update (20.12.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16