

PEW 8.286 crimping pliers

PEW 8.186 Crimping tool/pliers for pressing insulated conductor end sleeves with a hexagonal crimping, made in Germany, quick and reliable



Benefits

- Ergonomic handles and very low hand force required
- Automatic self-adjustment to requested wire size
- DIN compliant crimping quality due to integral lock (self-releasing mechanism)
- Uniform feed on the crimp die guarantees exact crimping profiles

Application range

For pressing insulated and non-insulated conductor end sleeves
Could be used up to a sleeve length of 20 mm (for sleeves longer than 12 mm at least 2 crimps are necessary)

Product features

Made of chromium-plated tool steel

Note

End sleeves up to 12 mm only needs to be pressed once, longer end sleeves (up to a 20 mm lengths) needs to be pressed at least twice

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000168

ETIM 5.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000168

ETIM 6.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

PEW 8.286 crimping pliers

Article number	Article designation	For mm ²	Crimping profile	Weight (kg)	Length (mm)	Pieces / PU
61813737	PEW 8.286	0.08 - 16.0	hexagon	0.38	180	1