

CSA 0760 + KSA 0760 crimping pliers

CSA/KSA 0760: Crimping pliers for pressing insulated connectors as insulated cable lugs and blade/panel connectors from 0,5-6mm², Crimping profile: oval, ergonomic design



Reliability

Benefits

- Clearly marked press moulds
- Less power required due to special mechanism
- Tested for a minimum of 80,000 pressings
- Pressing according to the forced finish system
- Cross-section of press matrix is embossed in the cable lugs for checking

Application range

The Miniforce tool for insulated connections of 0.5 - 6 mm²

Product features

Emergency release, if the pressing operation needs to be interrupted

Norm references / Approvals

Tested in accordance with DIN standard EN 60352-2

Product Make-up

CSA 0760: With C-frame, old design

KSA 0760: With K-frame- extremely long handles for two-handed operation, improved ergonomics

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000168

ETIM 5.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000168

ETIM 6.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection

Note:

Crimping profile: Oval

Last Update (18.12.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

CSA 0760 + KSA 0760 crimping pliers

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.



CSA 0760 + KSA 0760 crimping pliers

Article number	Article designation	For mm²	Crimping profile	Weight (kg)	Length (mm)	Pieces / PU
61722070	CSA 0760	0.5 - 6	oval	0.5	220	1
61790910	KSA 0760	0.5 - 6	oval	0.54	255	1
61751950	Spare spring CSA/KSA/DSA 0760	-	-	-	-	1
61722071	Crimping insert for CSA + KSA 0760	-	-	-	-	1