


TEB branch muff

TEB branch muffs with adhesive coating inside can be used for insulating and sealing of cable splices.



Good chemical resistance



Halogen-free



UV-resistant



Waterproof

Benefits

Secure sealing through thermoplastic adhesive coating on the inside

Good resistance to chemicals and solvents

Ensures high tensile strength and mechanical protection

Application range

Insulation and sealing of cable splices

Design

Double-walled

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001170

ETIM 5.0 Class-Description: Straight-through/transition joint (set)

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001170

ETIM 6.0 Class-Description: Branch-splice joint (set)

General:

UV-resistant

Info:

Shrinking ratio: > 2:1

Colour delivered:

Black

Material:

Cross-linked modified polyolefin, with thermoplastic adhesive coating inside

Halogen-free and silicone-free

Last Update (18.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

TEB branch muff

Temperature range: -55°C to +100 °C
Shrinking temperature: +120°C

Note

1. after shrinking +/- 10%; 2. after shrinking +/- 20%

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

TEB branch muff

Article number	Article description	Number of cores	H max. (mm)	H min. (mm)	K max. (mm)	K min. (mm)	P* mm	R* mm	Pieces / PU
61830110	TEB 2-30/12	2	30	12	14	4	93	23	10
61830120	TEB2-60/23	2	60	23	25	7.5	118	29	1
61830130	TEB3-60/24	3	60	24	27	7	165	50	1
61830140	TEB4-40/15	4	40	15	13	3	105	26	1
61830150	TEB4-55/21	4	55	21	20	5.5	150	40	1
61830160	TEB4-75/26	4	75	26	28	7.5	175	45	1
61830170	TEB4-90/32	4	90	34	32	10	198	58	1

Last Update (18.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16