

Insulating tube ISS

Insulating tube ISS made of silicone for bundling and insulating cables against heat, cold and temperature fluctuations (temperature resistance: -60 to 220 °C)



Good chemical resistance



Flame-retardant



Halogen-free



Corrosion-resistant



Temperature-resistant



UV-resistant

Benefits

Provides good insulation against heat, cold or temperature fluctuations
Resistant to most chemicals
Good weather and UV-resistance

Application range

Insulating tube

Note

Not suitable for shrinking

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002254

ETIM 5.0 Class-Description: Cable insulation hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002254

ETIM 6.0 Class-Description: Cable insulation hose

Last Update (05.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

Insulating tube ISS

Note:	Dielectric strength: 18 kV/mm
Material:	Silicone UV-resistant
Temperature range:	-60°C up to +220°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

Insulating tube ISS

Article number	Article designation	Colour	Internal Ø x wall thickness (mm)	Material	PU (m)
61760060	ISS 2	natural	2 x 0.4	Silicone	100
61760070	ISS 3	natural	3 x 0.4	Silicone	100
61760080	ISS 4	natural	4 x 0.75	Silicone	100
61760090	ISS 5	natural	5 x 0.9	Silicone	100
61760100	ISS 6	natural	6 x 0.9	Silicone	100
61760110	ISS 7	natural	7 x 0.9	Silicone	100
61760120	ISS 8	natural	8 x 1	Silicone	50
61760130	ISS 9	natural	9 x 1.05	Silicone	50
61760140	ISS 10	natural	10 x 1.05	Silicone	50

Last Update (05.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16